



ALTERNATE MACHINE ROOM LAYOUT

SCALE - 1" = 1'

NOTE: ALL DIMENSIONS ARE APPROXIMATE

DRAWN:	CHECKED:	DATE:	REVISION
G.P.	M.C.	01/08/04	NEW DRAWING
G.P.	M.C.	12/27/06	ADD DOOR CLEARANCES
G.P.	F.P.	01/13/16	CHANGE PUMPING UNIT DIMENSIONS

NOTES:

- ① 220 V, 2 POLE, SINGLE PHASE, FUSED DISCONNECT WITH 20 AMP RK-5 FUSES (PER NEC 2002 - BY OTHERS.) ALSO, PROVIDE 120 V., FUSED DISCONNECT OR 15 AMP CIRCUIT BREAKER FOR CAB LIGHTS (PER NEC 2002 - BY OTHERS.)
- ② PROVIDE A PHONE LINE TO THE ELEVATOR MACHINE ROOM AND INSTALL IN A 4" x 4" BOX WITH COVER (8' - 10' TAIL MIN.) (BY OTHERS.)
- ③ LIGHT SWITCH TO BE INSTALLED ADJACENT TO LOCK SIDE OF THE DOOR (BY OTHERS.)
- ④ MACHINE ROOM DOOR TO BE A MINIMUM OF 30" WIDE (BY OTHERS.)
- ⑤ A GFI RECEPTACLE IS TO BE PROVIDED IN THE ELEVATOR MACHINE ROOM / SPACE (PER NEC 2002 - BY OTHERS.)
- ⑥ 5'-0" MIN. HEADROOM REQ'D FOR ELEVATED PLATFORM/ STANDS.
- ⑦ FLOOR MOUNT PUMPING UNIT DIMENSIONS: 29" W x 16-1/2" D x 27-1/2" H



20 RESIDENTIAL DRIVE
CRAWFORDVILLE, FL
32327

ResidentialElevators.com

1-800-832-2004

JOB NAME:

ALTERNATE MACHINE ROOM
SPECIFICATIONS

DRAWING NUMBER

HYD M02